


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YSR28FX4CFXLTKITC
 781810473863
 HYRDC 4/0F- 4F STD CLR
 Active

Web Use
 BURNDY Product Line

Length (in)
 B Length (in)
 Strip Length

Dimensional

3.10
 1.43
 1.36

General

Product Description

Cu compression reducer splice kit-
 Code & Flex, W/Insp Hole, 4/0
 AWG(Brl A) #4 AWG Flex(Brl B),
 Purple(Brl A) Grey(Brl B), 15(Brl A)
 8(BrlB) Index

Conductor(s)

Flex (Class H) Side A - Range
 Flex (Class M) Side B - Range
 Flex (Class K) Side A - Range
 Flex (Class G) Side B - Range
 Flex (Class I) Side A - Range
 Flex (Class H) Side B - Range
 Flex (Class I) Side B - Range
 Flex (Class M) Side A - Range
 Flex (Class G) Side A - Range
 Flex (Class K) Side B - Range

4/0 AWG
 4 AWG
 4/0 AWG
 4 AWG
 4/0 AWG
 4 AWG
 4 AWG
 4/0 AWG
 4/0 AWG
 4 AWG

Physical

Type of Plating
 Plated (Yes or No)

Tin - Electro Plated
 Y

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

N
 N
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175