


[On Line Catalog](#)


**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YSR29FX28LTCKITC  
 781810415825  
 HYRDC 4/0F-4/0F STD CLR  
 Active

**Web Use**  
 BURNDY Product Line

Length (in)  
 B Length (in)  
 Strip Length

#### Dimensional

3.00  
 1.44  
 1.38

#### General

Product Description

Copper Compression Reducer; 3  
 IN L; 15 Index (Brrl A), 16 Index  
 (Brrl B); 4/0 AWG FLEX (Brrl A);  
 4/0 AWG STR (Brrl B)

#### Conductor(s)

Flex (Class H) Side A - Range N/A  
 Flex (Class M) Side B - Range N/A  
 Flex (Class K) Side A - Range 4/0 AWG  
 Flex (Class G) Side B - Range N/A  
 Flex (Class I) Side A - Range 4/0 AWG  
 Flex (Class H) Side B - Range N/A  
 Flex (Class I) Side B - Range N/A  
 Flex (Class M) Side A - Range 4/0 AWG  
 Flex (Class G) Side A - Range N/A  
 Flex (Class K) Side B - Range N/A

#### Physical

Type of Plating Tin - Electro Plated  
 Plated (Yes or No) Y

#### Approvals / Certifications

UL Listed N  
 CSA Certified N  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N

#### Documentation

**For further technical assistance, please contact us**

#### BURNDY LLC - USA

47, industrial Park Drive  
 Manchester NH03109

#### BURNDY Technical Servcies

47, industrial Park Drive  
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM  
 Monday - Friday  
 Phone: 000-346-4175