


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YSR3125FXLTCKITC
 781810345337
 HYRDC 350C-1/0F STD CLR
 Active

Web Use
 BURNDY Product Line

Length (in)
 B Length (in)
 Strip Length

Dimensional

3.33
 1.49
 1.41

General

Product Description

In-line Reducer splice kit, 350
 kcmil code(Brl A) 1/0 AWG flex or
 code(Brl B), Tin plated, Red(Brl A)
 Pink(Brl B), 18(Brl A) 12(Brl B)
 index

Conductor(s)

Flex (Class H) Side A - Range N/A
 Flex (Class M) Side B - Range 1/0 AWG
 Flex (Class K) Side A - Range N/A
 Flex (Class G) Side B - Range 1/0 AWG
 Flex (Class I) Side A - Range N/A
 Flex (Class H) Side B - Range 1/0 AWG
 Flex (Class I) Side B - Range 1/0 AWG
 Flex (Class M) Side A - Range N/A
 Flex (Class G) Side A - Range N/A
 Flex (Class K) Side B - Range 1/0 AWG

Physical

Type of Plating Tin - Electro Plated
 Plated (Yes or No) Y

Approvals / Certifications

UL Listed N
 CSA Certified N
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175