


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YSR32FX28FXLTCKITC
 781810345207
 HYRDC 300F-4/0F STD CLR
 Active

Web Use
 BURNDY Product Line

Dimensional

Bar Length (in)	3.46
Length (in)	3.46
Barrell Style	Skived
Barrel Type	Standard
B Length (in)	1.57
Strip Length Run	1.36
Strip Length Tap	1-3/8
BB - Length (in)	1.43

Conductor(s)

Flex (Class H) Side A - Range	300 kcmil
Flex (Class M) Side B - Range	N/A
Flex (Class K) Side A - Range	300 kcmil
Flex (Class G) Side B - Range	N/A
Flex (Class I) Side A - Range	300 kcmil
Flex (Class H) Side B - Range	N/A
Flex (Class I) Side B - Range	N/A
Flex (Class M) Side A - Range	300 kcmil
Flex (Class G) Side A - Range	300 kcmil
Flex (Class K) Side B - Range	N/A
Copper Str Size (Side A) - Range	N/A

Approvals / Certifications

UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Physical

Color Code (Side A)	Red
Type of Plating	Tin - Electro Plated
Color Code (Side B)	Purple
Connector Type	Splice,Reducer
Die Index (Side B)	15
Die Index (Side A)	19,L80
Plated (Yes or No)	Y
Product Material	Copper

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175