



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YSR3434FXLTCKITC
781810472347
HYRDC 500C-350F STD CLR
Active

Web Use
BURNDY Product Line

Length (in)
B Length (in)
Strip Length

Dimensional

3.51
1.69
1.60

General

Product Description

Cu compr reducer splice kit-Code
& Flex, W/Insp Hole, 500kcmil
code(Brl A) 350kcmil flex(Brl B),
Brown (Brl A)Blue(Brl B), 20(Brl A)
19 or L80(Brl B) Index

Conductor(s)

Flex (Class H) Side A - Range N/A
Flex (Class M) Side B - Range 350 kcmil
Flex (Class K) Side A - Range N/A
Flex (Class G) Side B - Range 350 kcmil
Flex (Class I) Side A - Range N/A
Flex (Class H) Side B - Range 350 kcmil
Flex (Class I) Side B - Range 350 kcmil
Flex (Class M) Side A - Range N/A
Flex (Class G) Side A - Range N/A
Flex (Class K) Side B - Range 350 kcmil

Physical

Type of Plating Tin - Electro Plated
Plated (Yes or No) Y

Approvals / Certifications

UL Listed N
CSA Certified N
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175