


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YSR38FX34FXLTCKITC
 781810472323
 HYRDC 500F-350F STD CLR
 Active

Web Use
 BURNDY Product Line

Length (in)
 B Length (in)
 Strip Length

Dimensional

4.06
 1.88
 1.77

General

Product Description

Cu compr reducer splice kit-Code
 & Flex, W/Insp Hole, 500kcmil
 flex(Brl A) 350kcmil flex(Brl B),
 Pink (Brl A)Blue(Brl B), L99(Brl A)
 19 or L80(Brl B) Index

Conductor(s)

Flex (Class H) Side A - Range
 Flex (Class M) Side B - Range
 Flex (Class K) Side A - Range
 Flex (Class G) Side B - Range
 Flex (Class I) Side A - Range
 Flex (Class H) Side B - Range
 Flex (Class I) Side B - Range
 Flex (Class M) Side A - Range
 Flex (Class G) Side A - Range
 Flex (Class K) Side B - Range

500
 350
 500
 350
 500
 350
 350
 500
 500
 350

Physical

Type of Plating
 Plated (Yes or No)

Tin - Electro Plated
 Y

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

N
 N
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175