



BURNDY Catalog Number
UPC Number
Description
Status

YSR4CFX10CLTCKITC
781810473955
HYRDC 4F- 10F STD CLR
Active

Web Use
BURNDY Product Line

Length (in)
B Length (in)
Strip Length

Dimensional

1.66
0.74
0.71

General

Cu compression reducer splice kit-
Code & Flex, W/Insp Hole, #4AWG
Flex or code(Brl A) #10 AWG Flex
or code(Brl B), Grey(Brl A), 8(Brl
A) Index

Product Description

Conductor(s)

Flex (Class H) Side A - Range
Flex (Class M) Side B - Range
Flex (Class K) Side A - Range
Flex (Class G) Side B - Range
Flex (Class I) Side A - Range
Flex (Class H) Side B - Range
Flex (Class I) Side B - Range
Flex (Class M) Side A - Range
Flex (Class G) Side A - Range
Flex (Class K) Side B - Range

4
14
4
14
4
14
14
4
4
14

Physical

Type of Plating
Plated (Yes or No)

Tin - Electro Plated
Y

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

N
N
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Services

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175