



On Line Catalog



BURNDY Catalog Number	YSV1014G2
UPC Number	781810026403
Description	20-10 STR/SOL/FX BUTT SP
Status	Active

Web Use
BURNDY Product Line

Barrell Style
B Length (in)

Dimensional

Chamfered
0.31

General

Product Description

Copper Reducer Butt Splice, 20-10
AWG, 0.83" Splice Length, Tin
Plated

Conductor(s)

Flex (Class H) Side A - Range	10
Aircraft Cable Size (Range)	N/A
Flex (Class M) Side B - Range	20-14
Flex (Class K) Side A - Range	10
Flex (Class G) Side B - Range	20-14
Flex (Class I) Side A - Range	10
Flex (Class H) Side B - Range	20-14
Flex (Class I) Side B - Range	20-14
Copper Solid Size (Range)	N/A
Flex (Class M) Side A - Range	10
Flex (Class G) Side A - Range	10
Flex (Class K) Side B - Range	20-14
Copper Stranded (Range)	20-10

Physical

Type of Plating
Plated (Yes or No)

Tin
Y

Approvals / Certifications

UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175