

Sentry Switched CDU

Key Features

- > **High Density:** Single-power input feed; 24 outlets per enclosure (Qty 24 IEC C13 outlets)
- > **Power Distribution:**
208-240V, 20A and 30A; 230V 16A and 32A power input feed options
- > **Input Current Monitor:**
Precisely measure the aggregate current draw (in amps) of the circuit. On-site verification of the input current with LED digital display. Remote verification via web browser or serial screen.
- > **Network Power Management:** Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, TACACS, RADIUS, and RS-232 access
- > **SNMP Traps and Email alerts:** Provide automated alerts for power and environmental conditions
- > **Environmental Monitoring:**
Each Switched CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > **Add an Expansion Module:**
Daisy chain the Switched CDU Expansion Module (CXG) for power monitoring of separate power circuits from a single IP address

CWG-24V2/VE Switched POPS™ CDU with C13 Outlets and PIPS™

High-Density Power Distribution

The Switched CDU combines network configuration and management with power distribution, environmental monitoring and the ability to provide power monitoring per an individual outlet/device. Power information per outlet includes current, voltage, power (kW), apparent power (VA), crest factor and power factor. Reboot a single or dual-power server with one command. Receive SNMP or email-based alerts when power or environmental conditions exceed thresholds. Assign user specific access rights to designated outlets or groups.

This Switched CDU has a middle entry for network, serial, and environmental connections combined with a top power cord entry. Current monitors are easily inverted via the web GUI or serial interface. This provides flexibility when connecting Switched CDU's with overhead power or raised floor installations.

Additional Benefits:



POPS™ (Per Outlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor and Power Factor per outlet at an accuracy of $\pm 2\%$.



Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protections
> UL-489 rated circuit breakers



PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, Reactance, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.



Temperature and Humidity

The Switched CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CWG-24V2A458 CXG-24V2A458*	208-240V 50/60Hz	20A	IEC C20 Inlet, Top Cord Entry	(24) IEC 60320/C13	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)
CWG-24V2C458 CXG-24V2C458*	208-240V 50/60Hz	30A	NEMA L6-30P Plug, 10'(3m), Top Cord Entry	(24) IEC 60320/C13	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)
CWG-24VEA458 CXG-24VEA458*	230V 50/60Hz	16A	IEC C20 Inlet, Top Cord Entry	(24) IEC 60320/C13	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)
CWG-24VEK458 CXG-24VEK458*	230V 50/60Hz	32A	IEC Blue 2P+G Plug, 10'(3m), Top Cord Entry	(24) IEC 60320/C13	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)

* CXG part numbers refer to the Expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2007 and CAN/CSA 22.2 No. 60950-1-07
- > European Union (TUVGS mark) to EN 60950-1:2006 + A11
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2/v3
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)
- > IPv6

Power Cord Options

- > PTCORD-1 IEC 60320/C19 - NEMA L6-20P, 10ft (3m)
- > PTCORD-2 IEC 60320/C19 - Schuko 10ft (3m)
- > PTCORD-3 IEC 60320/C19 - IEC 60309 (BS4343, CEE17) 16/20A Blue (UK Commando) 10ft (3m)
- > PTCORD-4 IEC 60320/C19 - BS1363 13A (UK) 10ft (3m)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager):
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information
 - Optional Appliance or virtual version
 - SPM v5.1+ is VMware READY

vmware
READY

VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions

1U SPM Appliance



Expansion Module
Model Numbers

- > CXG-24V2A458
- > CXG-24V2C458
- > CXG-24VEA458
- > CXG-24VEK458



Server Technology

HEADQUARTERS -
NORTH AMERICA
Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

Western Europe, Middle East and
Africa
Server Technology
Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com

Central Europe, Eastern Europe and
Russia
Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
salesint@servertech.com

APAC
Server Technology
Room 2301, 23/F, Future Plaza
111-113 How Ming Street,
Kwun Tong, Hong Kong
Direct line: +852 3916 2048
Fax Line: +852 3916 2002
salesint@servertech.com