

APC Back-UPS® 750

Best Value Battery Backup & Protection for Home and Home Office Computers

APC's Back-UPS 750 provides enough battery backup power so you can work through medium length power outages. It also safeguards your equipment against damaging surges and spikes that travel along utility and data lines. The Back-UPS 750 is also "greener" than ever, with power saving outlets that turn off power to three of your peripherals when ever your computer is turned off or goes into standby mode. And its ultra-efficient design consumes less power during normal operation than any other battery backup in its class. Together, these power-saving features can save an average of \$40/year on your electricity bill*. Coupled with the standard features of the Back-UPS series, the 750 is the perfect unit to protect your productivity from the constant threat of bad power and lost data.

* \$40 savings based on comparable competitive models, and is comprised of an ultra-efficient electrical design, and power-saving "Master" and "Controlled" outlets (assumes three hours of daily computer use at \$0.10/kw hr, with three peripherals plugged into 'Controlled' outlets: 3-in-1 printer, speakers, external storage device).

Product Features:



- 1 **5 "Battery Backup & Surge" Outlets** keep CPU, monitor and another critical device running when the power goes out or fluctuates outside safe levels.
- 2 **5 "Surge Only" Outlets** protect printers, faxes or other equipment without reducing battery capacity (including three power-saving "Controlled" outlets).
- 3 **PowerChute Software** lets you use your computer to access additional power protection and management features:
 - Preserves your work, shuts down system during outages
 - Restarts your system, minimizing work disruptions
 - Enables customization of your Back-UPS settings
 - Monitors and displays power and battery status
- 4 **Data Line Surge Protection** guards against surges and spikes traveling over phone, network and coax cable lines.
- 5 **Combination Power Button/LED Indicator** provides visual and audible status of unit.
- 6 **Ultra Efficient Electrical Design**, RoHS compliance and all recyclable packaging materials minimize environmental impact and maximize efficiency.
- 7 **Building Wiring Fault Indicator** lets you know if there are problems in your building's wiring.
- 8 **Push Button Circuit Breaker** enables quick recovery from overload.
- 9 **Automatic Diagnostic Testing** ensures your unit is ready when you need it.
- 10 **3 Yr Warranty**, \$75,000 Equipment Protection Policy, free technical phone and online support.

APC
by Schneider Electric

Back-UPS 750 Specifications

Model Number	BE750G
Output	
Output Capacity	750 VA / 450 Watts
Output Voltage, Frequency (On utility)	120V, 50 or 60Hz (auto-sensing)
Output Voltage, Frequency (On battery)	115V +/-8%, 50 or 60 Hz +/-3Hz (auto-sensing)
Output Connections	10 total NEMA 5-15R outlets: 5 battery backup & surge 5 surge protection only (incl. 3 <i>Controlled</i> outlets)
Waveform Type	Stepped Approximation to Sine Wave
Input	
Input Voltage / Frequency	120V, 50 or 60 Hz
Input Connection	6 ft cord with right angle plug (NEMA 5-15P)
Surge Protection	
AC Power Surge Protection	All outlets
Data Line Surge Protection	Analog phone line (Fax/Modem/DSL) Network line (Ethernet 10/100 Base-T) Coax cable (CATV, SATV, modem, A/V)
Physical	
Unit Dimensions (H x W x D)	13.5" x 7.1" x 3.5"
Unit Weight	10.34 lbs
Shipping Dimensions (H x W x D)	17.8" x 10.2"x 5.94"
Shipping Weight	12.54 lbs
Color	Black
UPC Code	731304256601
Battery	
Battery Type	Maintenance-free, sealed lead-acid battery, leakproof
Management	
Alarms	Visual (LED) and audible alarms
Auto-Shutdown Software	PowerChute Personal Edition (via USB interface)
Safety	
Certification/Approvals	TUV, UL1778, CSA C22.2 No.107.1, FCC Part 68 & Part 15 Class B, NOM

APC by Schneider Electric

132 Fairgrounds Rd
West Kingston, RI 02892
Tel: 800-800-4272
www.apc.com

