

APC Performance SurgeArrest 11 Outlet with Phone (Splitter), Coax and Ethernet Protection

Maximum Power Surge Protection for Computers, Notebooks and Other Electronics



The APC SurgeArrest® Performance series offers our highest level of power surge protection for your professional computers, electronics and connected devices, as well as providing surge protection for all of your data lines. The P11VNT3 model offers a 3020 joule rating, 11 outlets (six are block-spaced) and a 180 degree rotating eight foot power cord. Network, telephone and coax cable line surge suppression jacks are available to protect against dangerous surges traveling along data lines. Finally, APC's lifetime product warranty and equipment protection policy guarantees customer peace of mind!

Basic Product Features

- **Guaranteed protection & lifetime warranty** means peace of mind
- **Ethernet data line protection**
- **Phone line protection jacks with splitter**
- **Coax cable / video protection jacks**
- **8 ft Power Cord with rt. Angle Plug**
- **Wiring Fault LED** proactively notifies you of potentially dangerous building wiring conditions
- **Working Protection LED** proactively notifies you when the unit needs a free replacement

Protection

Multi-Stage Surge Protection circuitry ensures protection that is guaranteed for life. All three power modes (L-N, L-G, N-G) are protected. Reliable thermal fusing helps ensure safe operation under all conditions.

Noise Filter reduces Electromagnetic Interference (EMI) to help avoid equipment lock-up.

Ethernet, coaxial cable and phone line protection ensures complete protection of your equipment from surges. It is very important to protect your equipment from "back door" electric surges traveling through data lines, as they can be as damaging to your equipment as surges traveling over power lines.

Safety-Agency Approved means the product has been tested and approved to work safely with the connected service provider equipment and within the specified environment. UL, FCC approvals. Listed to UL1449 3rd Edition standard by CSA.

Features and Specifications



MODEL	P11VNT3
ERP	\$49.99
Voltage and Frequency	120V, 50/60Hz
Cord length and plug type	8' with right angle NEMA 5-15P
Joule rating	3020
Let Through Voltage Rating	< 40
# of outlets	11 (6 spaced for block plugs)
Wiring Fault & Protection Wkg LEDs	Yes
Data line protection	Tel, Network, and coax cable line protection
Wall-mountable	Yes
UL Rating	330V
Safety Approvals	UL1449 3 rd Edition, UL1363
Product Warranty	Lifetime
Equipment Protection Policy*	\$100,000

*APC will pay to repair or replace properly connected equipment if damaged by a power transient while connected to an APC surge protector. See Equipment Protection policy (included with unit) for details.