

# Speaker Selectors • Subwoofer Speakers

www.specotech.com • 1-800-645-5516

## STEREO SPEAKER SYSTEM FOR UP TO 5 PAIRS OF SPEAKERS

- 50 watts RMS power handling per channel
- Control each pair independently
- Stereo phone jack for monitoring
- Circuit breaker protection
- Maintains impedance • 4"L x 8"W x 2.5"H



SSB-5

## STEREO SPEAKER DISTRIBUTION CENTERS

- Up to 4 (SDC-4VC) or 6 (SDC-6VC) speaker pairs can be independently controlled
- Each zone has an ON/OFF switch, an A/B source selector and a volume control
- Sleek black appearance blends in with other audio equipment.
- There is zero power loss in each zone when all four (SDC-4VC) or six (SDC-6VC) controls are set at maximum volume. • The distribution center will equally distribute the sound to each of the speaker pairs without power loss.
- Power handling capability of up to 72 watts RMS continuous (216 watts audio) at 8 Ohm in any switching mode • Automatic impedance matching
- Special circuitry used to avoid overheating.
- Heavy duty screw-type connectors are provided on the rear panel to ensure long lasting low loss connections



4 stereo speaker outputs **SDC-4VC** 6 stereo speaker outputs **SDC-6VC**

## STEREO SPEAKER SELECTOR 180 WATTS RMS POWER HANDLING

- High power handling • 2 amplifier input
- Controls 6 pairs of speakers • For 4,8,16 Ohm systems
- Output switching from amplifier A or B to 6 independently controlled pairs of speakers
- Impedance matching • Circuit breaker protection
- Quick disconnect connectors
- 14"L x 7"W x 2.75"H



SLS-6

## PROGRAMMABLE 12 SPEAKER CONTROLLER WITH 6 VOLUME CONTROLS AND 2 SELECTABLE INPUT SOURCES

Similar specifications of the SDC-6VC plus:

- 12 mono speaker outputs handling up to 25W RMS continuous at 70V per speaker output
- 12 position rotary switches
- Screw-tight type connectors
- Amplifier recommendation: 120W RMS at 70V (not to exceed 25W RMS per speaker output)



SDC-6VC/70

## STEREO SPEAKER DISTRIBUTION CENTER

- 100 watts RMS power handling per channel
- 300 watts Max. • Allows for easy expansion for 1 pair of amplifier speaker outputs to up to 8 pairs of speaker outputs (1 pair in to 8 pair out)
- 15"L x 1.5"W x 3.25"H



SDS-8

## 12" AMPLIFIED HOME THEATER SUBWOOFER

- 100 watts RMS amplifier • 120 watts max
- 8 Ohm impedance • 12" woofer
- Freq. response 20 Hz-180 Hz • Adjustable crossover
- Gain control port
- Accepts line level or powered input
- Line level output
- Black wood grain cabinet
- 16"L x 15.7"W x 15.2"H
- On/Off/Auto power switch



SW-12A

## DECORATIVE STYLE STEREO WALL MOUNT SPEAKER SELECTOR

- Controls up to 7 pair of speakers independently with heavy duty rocker type switches
- 2 amplifier inputs (A or B)
- 75 watts RMS
- 150 watts max per channel
- Maintains impedance of 4,8,16 Ohm speakers
- Complete with heavy duty triple gang plate
- Available in white only



DVC-200

## HOME THEATER SUBWOOFER SYSTEM, 8" PORTED, 50 WATTS RMS

- Black wood cabinet • 50 watts RMS
- 100 watt peak power handling
- Satellite speaker controls
- Black wood cabinet
- Twin ported enclosure
- 8 Ohm impedance • Dual voice coil
- Frequency response: 35-240 Hz
- 20"L x 12.75"W x 6.5"H • 20 lbs.



SW-850