

1080p HD-SDI Indoor Dome Camera

HHDI04D1B 2.8 - 12mm auto iris varifocal lens, black housing
HHDI04D1W 2.8 - 12mm auto iris varifocal lens, white housing

Features

- 1/3" Sony CMOS image sensor
- 2.1M Pixels Full-HD video resolution
- Supports 1080p and 720p
- Simultaneous analog composite video output for easy service & camera installation
- 3-axis wall and ceiling mount
- Full OSD operation
- Lined dome cover
- 12VDC / 24VAC dual voltage operation
- 5 year warranty

Specifications

Image Sensor 1/3" Sony CMOS image sensor
Resolution..... 1920 x 1080p
Minimum Illumination..... 0.5 lux @ F1.2, 0.01 lux (sense-up x60)
Effective Pixels 1944 (H) x 1092 (V), 2.12M pixels
Scanning System..... Progressive
S/N Ratio More than 50dB (AGC off)
Shutter Speed..... Auto, 1/60 sec. – 1/10,000 sec., x2-x30
Sense-Up..... Off / Auto x2-x32
Day/Night..... Color / BW / Auto / EXT
Lens Type DC / Manual
AGC..... High / Middle / Low / Off
White Balance ATW / AWC - SET / Indoor / Outdoor / Manual
DNR..... High / Middle / Low / Off



WDR High / Middle / Low / Off
BLC / HSBL Off / BLC / HSBL
Sharpness 1-100 level adjustable
Digital Zoom x64 (PIP)
Motion Detection..... 3 zone
Privacy..... 8 zone
Video Output..... HD-SDI, CVBS simultaneously
Power Supply 12VDC / 24VAC dual voltage operation
(power supply not included)
Power Consumption 12VDC, 250mA / 24VAC, 150mA
Operating Temperature..... -4° F – 140° F
Dimensions..... 3.94" (H) x 5.51" (Dia.)
Weight 1 lb.

Optional Accessories



Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 2/6/13

For more information contact Speco Technologies
200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com