



SAFETY DATA SHEET

AEROSPEC 300

Page: 1

Compilation date: 30/09/2014

Revision No: 6

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: AEROSPEC 300

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Multi-purpose grease

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319

Classification under CHIP: -: R52/53

Most important adverse effects: Causes serious eye irritation.

2.2. Label elements

Label elements under CLP:

Hazard statements: H319: Causes serious eye irritation.

Signal words: Warning

Hazard pictograms: GHS07: Exclamation mark



Precautionary statements: P264: Wash thoroughly after handling.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove

[cont...]

SAFETY DATA SHEET

AEROSPEC 300

Page: 2

contact lenses, if present and easy to do. Continue rinsing.

P337+313: If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

EINECS	CAS	CHIP Classification	CLP Classification	Percent
265-166-0	64742-62-7	Substance with a Community workplace exposure limit.	-	10-30%

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

224-235-5	4259-15-8	-	Eye Dam. 1: H318; Aquatic Chronic 2: H411	<2%
-----------	-----------	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Use water spray to cool containers. Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

SAFETY DATA SHEET

AEROSPEC 300

Page: 3

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

SOLVENT REFINED BASE OIL (NOTE L- LESS THAN 3% DMSO EXTRACT)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	-	5 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Respiratory protection: Respiratory protection not normally required.

Hand protection: Protective gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

[cont...]

SAFETY DATA SHEET

AEROSPEC 300

Page: 4

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Brown

Odour: Barely perceptible odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: Highly viscous

Melting point/range°C: > 280

Flash point°C: > 200

Autoflammability°C: > 200

Relative density: < 1

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

DERMAL	RBT	LD50	>5000	mg/kg
ORAL	RAT	LD50	>3100	mg/kg

Toxicity values: No data available.

[cont...]

SAFETY DATA SHEET

AEROSPEC 300

Page: 5

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

2-ETHYLHEXYL ZINC DITHIOPHOSPHATE

ALGAE	72H ErC50	>240	mg/l
DAPHNIA	48H EC50	1 - 10	mg/l
FISH	96H LC50	1 - 10	mg/l

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

[cont...]

SAFETY DATA SHEET

AEROSPEC 300

Page: 6

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legend to abbreviations: PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.