


1 2 3 4 5 6

A


B

C

D



Kontakt für Schlauchinnendurchmesser 3,0 mm
tube fitting insert for tubing size ID 3,0 mm



			All Dimensions in mm Original Size DIN A 4				Techn. Character.			Nicht tolerierte Maße/Free size tolerances		
				Dat.	Name	Maßstab/Scale 2:1	Han-Modular Pneumatikstiftkontakt <i>pneumatic male tube fitting insert</i>					
			Detail.	20.10.98	SPER							
			Insp.		SDT							
			Stand.									
413153	27.08.07	Bor	HARTING Electric GmbH & Co. KG D-32339 Espelkamp					TB 09 14 000 6152			Blatt/ page /	
27321	07.03.00	Gü						Sub. TB 09 14 000 6... v. 23.06.94				
Mod.	Dat.	Name										

