





|                                                                                     |  |                                              |                 |                                                            |                 |                           |   |                             |      |                    |  |                                                          |  |             |
|-------------------------------------------------------------------------------------|--|----------------------------------------------|-----------------|------------------------------------------------------------|-----------------|---------------------------|---|-----------------------------|------|--------------------|--|----------------------------------------------------------|--|-------------|
| Coating                                                                             |  | A=                                           | mm <sup>2</sup> | V=                                                         | mm <sup>3</sup> | m=                        | g | Mat.                        |      |                    |  |                                                          |  |             |
|  |  | All Dimensions in mm<br>Original Size DIN A4 |                 | Scale<br>2:1                                               |                 | Free size tol.            |   |                             | Ref. |                    |  |                                                          |  |             |
|                                                                                     |  |                                              |                 |                                                            |                 |                           |   |                             | Sub. |                    |  |                                                          |  |             |
|  |  | All rights reserved                          |                 | Created by<br>RULLKOETTER                                  |                 | Inspected by<br>SCHNIEDER |   | Standardisation<br>TIEMANNA |      | Date<br>2014-06-11 |  | State<br>Final Release                                   |  |             |
|                                                                                     |  | Department EL PD - DE                        |                 | Title<br>Han 100A axial module, male 10-25 mm <sup>2</sup> |                 |                           |   |                             |      |                    |  | Doc-Key / ECM-Nr.<br>100195634/UGD/004/A<br>500000074632 |  |             |
| HARTING Electric GmbH & Co. KG<br>D-32339 Espelkamp                                 |  |                                              |                 | Type<br>TB                                                 |                 | Number<br>09 14 002 2653  |   |                             |      |                    |  | Rev.<br>A                                                |  | Page<br>1/1 |
|                                                                                     |  |                                              |                 |                                                            |                 |                           |   |                             |      |                    |  |                                                          |  |             |