



-For solid and stranded conductors  
 AWG 27 up to AWG 22  
 -Max. wire diameter 1.5mm  
 -Cable diameter 6 - 12mm  
 -Degree of protection IP65/IP67  
 -Cat. 6 performance class EA  
 suitable for 1/10 Gigabit Ethernet  
 -Temperature range -40°C up to +70°C  
 -750 mating cycles

Data contact plating: Au 1.27µm (50µ") over nickel

			Det.	Name	 All Dim. in mm Orig. Size DIN A 4	Han 3A RJ45 Hybrid 10G plug plastic version	Maßstab/ Scale 1,5:1
		Insp.					
		Stand.					
36080	21/10/09	AB	HARTING EURL F-95972 Paris			TB 09 45 125 1760	Blatt/ Page 1 / 1
Mod.	Det.	Name				Sub.	