

5

4

3

2


1

D

C



B


A



Connector pitch on panel
Axis X=27mm and Axis Y=21mm

(1) screwing torque: 0.3 to 0.5N.m
(2) screw between housing and PCB:
screw for plastic ϕ_{nom} 2.6mm
Lmax 6mm and screwing torque = 0.45 to 0.5N.m



Mod.	Dat.	Name	Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	RJ-Industrial Push Pull hybrid receptacle set M2.5 screws	Maßstab/ Scale 1.5:1
36099	03/11/10	AB	Detail.	04/09/07	AM		
34909	08/04/08	AB	Insp.				
34798	21/01/08	AB	Stand.				
34762	05/10/07	AM	HARTING EURL F-95972 Paris			TB 09 45 245 1300	Blatt/ Page 1 / 1
34600	04/09/07	AM					