



|                                                                                     |  |                                              |  |                                             |  |                          |  |                             |  |                    |  |                                                          |  |
|-------------------------------------------------------------------------------------|--|----------------------------------------------|--|---------------------------------------------|--|--------------------------|--|-----------------------------|--|--------------------|--|----------------------------------------------------------|--|
|  |  | All Dimensions in mm<br>Original Size DIN A4 |  | Scale<br>1:1                                |  | Free size tol.           |  | Ref.                        |  |                    |  |                                                          |  |
|                                                                                     |  |                                              |  |                                             |  |                          |  | Sub.                        |  |                    |  |                                                          |  |
|  |  | All rights reserved                          |  | Created by<br>RULLKOETTER                   |  | Inspected by<br>BERGHORN |  | Standardisation<br>TIEMANNA |  | Date<br>2013-08-14 |  | State<br>Final Release                                   |  |
| HARTING Electric GmbH & Co. KG<br>D-32339 Espelkamp                                 |  | Department EL PD - DE                        |  | Title<br>Han B Hood Top Entry LC 4 Pegs M20 |  |                          |  |                             |  |                    |  | Doc-Key / ECM-Nr.<br>100192233/UGD/004/A<br>500000065375 |  |
|                                                                                     |  |                                              |  | Type<br>TB                                  |  | Number<br>19 30 010 1420 |  |                             |  |                    |  | Rev.<br>A                                                |  |