

1 2 3 4 5 6


A

B

C

D

Gesamtlänge im verschraubten Zustand ca. 40,8mm  
 Complete length when assembled app. 40,8mm




X

M8x1


SW9  
 width across  
 flats 9

Ø 11,5

Y



Steckgesicht n.  
 Contact face acc. to  
 IEC 61076-2-104



Leiterquerschnitt conductor cross section	0,08 - 0,14 AWG26 - AWG22
Kabeldurchmesser cable outside diameter	1,9 - 3,5mm

	All Dimensions in mm Original Size DIN A4		Scale 2:1	Free size tol.		Ref.	
	All rights reserved Department EC PD - DE		Created by DYCKC	Inspected by WELLMANN	Standardisation HOFFMANN	Date 2013-01-22	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp			Title HARAX M8-XS male 3-pole			Doc-Key / ECM-Nr. 100213102/UGD/003/B 5300000857288	
			Type TB	Number 21021591305		Rev. B	Page 1/1