

5








4

3

2

1

1:1



Steckgesicht n.
Contact face acc.
IEC 61076-2-101

Leiterquerschnitt conductor cross section	0,34 - 0,75mm ² AWG22-AWG18
Kabeldurchmesser cable outside diameter	6,0-8,0mm

All Dimensions in mm Original Size DIN A 4			Techn. Character.			
EC01896	18.05.10	DY		Dat.	Name	Maßstab/Scale 2:1
412800	19.03.07	DY	Detail.	10.04.02	Pae	
411606	08.08.05	DY	Insp.		Sr	
410925	10.03.04	DY	Stand.			
410180	30.08.02	Pae				
410027						
Mod.	Dat.	Name	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			



Nicht tolerierte Maß/Free size tolerances	
Rundsteckverbinder/ Circular connector M12-L 4polig Stift/ M12-L 4poles male bleifrei/lead free	
TB 21 03 212 1305 Sub.	Blatt/ page /