


1 2 3 4 5 6

A

B


C

D




Montagehilfe wird lose beigelegt
assembly aid enclosed

X (2:1)



Steckgesicht n.
Contact face acc.to
IEC 61076-2-101

Crimpkontakte separat bestellen
Order contacts separately



Kabelø / Cableø			Leiterquerschnitt Wire gauge	Bestell-Nr. Part-No.
5,5-7,2mm	4,5-5,4mm	7.0-8.8mm		
Dichtung / Sealing			AWG 26-22	09 67 000 5576
schwarz/black	transparent	beige	AWG 24-20	09 67 000 8576

All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
				Dat.	Name	Maßstab/Scale 1:1	M12-L RSV geschirmt crimp, Stift, 4-polig, A-kodiert <i>Circular connector shielded crimp, male, 4-pole, A-coded</i>
			Detail.	06.03.07	Ho		
EC04038	10.11.11	DY	Insp.		SR		
EC03244	20.05.11	DY	Stand.				
EC02599	22.02.11	DY	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 21 03 812 1405
EC01106	23.11.09	DY					
Mod.	Dat.	Name				Sub.	Blatt/ page