





X (2:1)


Steckgesicht n.
Contact face acc.to
IEC 61076-2-101

Montagehilfe wird
lose beigelegt
assembly aid enclosed

Crimpkontakte separat bestellen
Order contacts separately

Kabelø cableø	Leiterquerschnitt Wire gauge	Bestell-Nr. Part-No.
4,5-8,8mm	AWG 26-22	09 67 000 5476
	AWG 24-20	09 67 000 8476
	alternativ/alternative	
	AWG 26-22	61 03 000 0096
	AWG 22-20	61 03 000 0074



 All Dimensions in mm Original Size DIN A 4			Techn. Character.				Nicht tolerierte Maß/Free size tolerances				
				Dat.	Name	Maßstab/Scale 1 : 1	M12-L RSV Buchse, crimp, geschirmt, 5-polig, A-kodiert Circular Connector female crimp, shielded, 5-pole, A-coded				
			Detail.	13.05.09	DY						
EC03731	30.08.11	DY	Insp.		WELL						
EC03243	20.05.11	DY	Stand.								
EC01106	23.11.09	DY	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP					TB 21 03 812 2505			Blatt/ page /
414334											
Mod.	Dat.	Name					Sub.				