


① only for four indent crimping tool adjusting Ø0,1



part no.		ØD	wire gauge		stripping length	
silver plated	gold plated		mm²	AWG		
09 15 000 6204	09 15 000 6224	0,90	0,14-0,37	26-22	8	
09 15 000 6203	09 15 000 6223	1,10	0,5	20		
09 15 000 6205	09 15 000 6225	1,30	0,75	18		
09 15 000 6202	09 15 000 6222	1,45	1	18		
09 15 000 6201	09 15 000 6221	1,75	1,5	16		
09 15 000 6206	09 15 000 6226	2,25	2,5	14	6	
09 15 000 6207	09 15 000 6227	0,90	0,14-0,37	26-22	8	

		All Dimensions in mm Original Size DIN A4		Scale 2:1		Free size tol.		Ref. Sub. TB 09 15 000 62.. v. 16.06.10						
		All rights reserved Department EL PD - DE		Created by RULLKOETTER		Inspected by SCHNIEDER		Standardisation TIEMANNA		Date 2014-05-20		State Final Release		
HARTING Electric GmbH & Co. KG D-32339 Espelkamp				Title Han D crimp contacts female								Doc-Key / ECM-Nr. 100109246/UGD/004/A 500000075030		
				Type TB		Number 09 15 000 62XX						Rev. A		Page 1/1