



Loading-Plan:



-Protection level: IP67
 -Temperature range: -20°C ...+60°C

13	09472222015	2x2xAWG22/7 outdoor PVC, Cat. 5+	40
12	09472222023		25
11	09472222013		20
10	09472222012		15
9	09472222011		10
8	09472222022		7.5
7	09472222006		5
6	09472222024		3.5
5	09472222005		3
4	09472222004		2
3	09472222003		1.5
2	09472222002		1
1	09472222001		0.5
Cont. No.	Part - no.	Type of cable	Dim. a[m]

	All rights reserved Department EC PD - RO	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.	Ref. Sub.		
		Created by TAMAS	Inspected by AVRAM	Standardisation HOFFMANN	Date 2014-06-26	State Final Release	Doc-Key / ECM-Nr. 100173941/UGD/011/C 50000076426	
HARTING Electronics GmbH D-32339 Espelkamp		Title M12 D-coded Cable Assembly			Type TB	Number 09472222XXX	Rev. C	Page 1/1