



- Protection level: IP65/67
 - Temperature range: -40°C ... +70°C

22	094 75555022		100
21	094 75555021		90
20	094 75555020		80
19	094 75555019		70
18	094 75555018		60
17	094 75555017		50
16	094 75555016		40
15	094 75555015		30
14	094 75555014		20
13	094 75555013		15
12	094 75555012		10
11	094 75555011		9
10	094 75555010		8
9	094 75555009		7
8	094 75555008		6
7	094 75555007		5
6	094 75555006		4
5	094 75555005		3
4	094 75555004		2
3	094 75555003		1.5
2	094 75555002		1
1	094 75555001		0.5
Cont. no.	Part no.	Type of cable	Dim. a[m]
		RJ Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	

	All Dimensions in mm Original Size DIN A3	Scale 1.5:1	Free size tol.	Ref.
	All rights reserved Department EC PD - RO	Created by MUNTEANV	Inspected by AVRAM	Standardisation HOFFMANN
HARTING Electronics GmbH D-32339 Espelkamp	Title RJ Industrial Cable Assembly			Date 2015-07-14
	Type TB	Number 094 75555XXX	Doc-Key / ECM-Nr. 100155398/UGD/004/B 500000090748	State Final Release
			Rev. B	Page 1/2

	1	2	3	4	5	6	7	8
A								
B	66	094 75555082	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green	100	110	094 75555182	HARTING PROFINET, Type C, torsional stress cable, 4-wire, Cat. 5, PUR, green	100
	65	094 75555081		90	109	094 75555181		90
	64	094 75555080		80	108	094 75555180		80
	63	094 75555079		70	107	094 75555179		70
	62	094 75555078		60	106	094 75555178		60
	61	094 75555077		50	105	094 75555177		50
	60	094 75555076		40	104	094 75555176		40
	59	094 75555075		30	103	094 75555175		30
	58	094 75555074		20	102	094 75555174		20
	57	094 75555073		15	101	094 75555173		15
	56	094 75555072		10	100	094 75555172		10
	55	094 75555071		9	99	094 75555171		9
	54	094 75555070		8	98	094 75555170		8
	53	094 75555069		7	97	094 75555169		7
	52	094 75555068		6	96	094 75555168		6
	51	094 75555067		5	95	094 75555167		5
	50	094 75555066		4	94	094 75555166		4
	49	094 75555065		3	93	094 75555165		3
	48	094 75555064	2	92	094 75555164	2		
	47	094 75555063	1.5	91	094 75555163	1.5		
	46	094 75555062	1	90	094 75555162	1		
	45	094 75555061	0.5	89	094 75555161	0.5		
	44	094 75555052	100	88	094 75555112	100		
D	43	094 75555051	90	87	094 75555111	90		
	42	094 75555050	80	86	094 75555110	80		
	41	094 75555049	70	85	094 75555109	70		
	40	094 75555048	60	84	094 75555108	60		
	39	094 75555047	50	83	094 75555107	50		
	38	094 75555046	40	82	094 75555106	40		
	37	094 75555045	30	81	094 75555105	30		
	36	094 75555044	20	80	094 75555104	20		
	35	094 75555043	15	79	094 75555103	15		
	34	094 75555042	10	78	094 75555102	10		
	33	094 75555041	9	77	094 75555101	9		
	32	094 75555040	8	76	094 75555100	8		
	31	094 75555039	7	75	094 75555099	7		
	30	094 75555038	6	74	094 75555098	6		
	29	094 75555037	5	73	094 75555097	5		
	28	094 75555036	4	72	094 75555096	4		
	27	094 75555035	3	71	094 75555095	3		
	26	094 75555034	2	70	094 75555094	2		
	25	094 75555033	1.5	69	094 75555093	1.5		
	24	094 75555032	1	68	094 75555092	1		
	23	094 75555031	0.5	67	094 75555091	0.5		
	Cont. no.	Part no.	Type of cable	Dim. a[m]	Cont. no.	Part no.	Type of cable	Dim. a[m]
F								

	All rights reserved Department EC PD - RO	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref. Sub.
	HARTING Electronics GmbH D-32339 Espelkamp	Created by MUNTEANV	Inspected by AVRAM	Standardisation HOFFMANN	Date 2015-07-14
		Title RJ Industrial Cable Assembly			Doc-Key / ECM-Nr. 100155398/UGD/004/B 500000090748
		Type TB	Number 094 75555XXX		Rev. B Page 2/2