

Waber-by-Tripp Lite 5-Outlet Industrial Power Strip, 15-ft. Cord, Switchless

MODEL NUMBER: **602-15**



Description

The Waber-by-Tripp Lite 602-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center spacing, 15-foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 602-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, 15-amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 5 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center outlet spacing
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15-amp power handling capacity with circuit breaker
- 15-foot AC line cord

Highlights

- 5 outlets
- 15-ft. cord
- 8.6-in. overall length
- No switch
- All-metal housing

Applications

- Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes the 602-15 ideal for distributing alternate waveform UPS or generator power to protected equipment.

Package Includes

- 602-15 Power Strip
- Warranty information
- Instruction manual

Specifications

General Info

RoHS

Y



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| OVERVIEW | |
|--|---|
| Style | Strip |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (5) 5-15R |
| Circuit Breaker (amps) | 15 |
| Outlet Spacing | 1.188 in. |
| Outlet Orientation | Single row of 5 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A 120V |
| Input Connection Type | NEMA 5-15P |
| Input Cord Length (ft.) | 15 |
| Input Cord Length (m) | 4.572 |
| Voltage Compatibility (VAC) | 120 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | No switch |
| PHYSICAL | |
| Unit Dimensions (hwd / in.) | 7.38 x 2.5 x 1.5 |
| Unit Dimensions (hwd / cm) | 18.7 x 6.35 x 3.8 |
| Material of Construction | Metal |
| Integrated Keyhole Mounting Tabs | Keyhole mounting tabs enable mounting to a variety of surfaces |
| Receptacle Color | Black |
| Color (AC Line Cord) | Black |
| Outlets Measurement (Center to Center) | 30mm |
| Keyhole Slot Mounting Measurement (Center to Center) | Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45 |
| CERTIFICATIONS | |
| UL1363 (Power Tap) | UL1363 |
| cUL / CSA (Canada) | cUL |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| WARRANTY | |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.