

## 8-Port Console KVM Switch w/19" LCD + 8 PS2/USB Combo Cables; TAA-Compliant

MODEL NUMBER: B020-U08-19KTAA



### Description

Tripp Lite's 8-port Console KVM Switch with 19" LCD is the optimal solution for controlling multiple computers from one keyboard, mouse and monitor. This single unit combines an 8 port KVM switch, keyboard, 19" LCD monitor and touchpad; all in a mere 1U of rack space. Stores neatly in the rack, pulls out when needed. Easily switch ports using the On-Console push buttons, On Screen Display (OSD) or keyboard hot key commands. Includes eight, six foot [Combo cable kits](#), which allow connection to either PS/2 or USB servers...no adapters needed. Includes a console cable kit that plugs into the port on the back of the unit, providing an extra HD15, (2) USB and (2) PS/2 ports that can be used to connect a Tripp Lite [B051-000](#) IP Remote Access Unit or an external console. Two USB ports are provided on the front of the unit: One for attachment of a separate USB mouse, and the other for attachment of USB peripherals, such as a flash drive, external hard drive, etc. to be shared between connected servers. Compatible with all major operating systems. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Constructed of heavy-duty steel housing.

### Features

- 1U rackmount console with built-in 8-Port KVM switch, 19" LCD screen, keyboard, and touchpad
- Includes (x8) P778-Series USB/PS2 combo KVM cable kits
- Additional ports are provided for the connection of an external console (PS/2 or USB) or IP remote access unit (model B051-000)
- Features a USB 1.1 port on the LCD panel for the sharing of USB peripherals such as Flash Drives and Card Readers amongst the connected computers
- Features a USB 1.1 port on the keyboard panel for the convenient connection of an external mouse
- USB/PS2 combo KVM cable kits allow you to connect to a USB or PS/2 computer without having to purchase separate cables or adapters
- OSD available in English, Spanish, French, German, and Japanese
- Switch ports via on-console pushbuttons, hotkey keyboard commands, or the OSD
- Auto scan feature allows for continuous scanning of connected computers

### Highlights

- 1U Rackmount console with built-in 8-Port KVM switch, 19" LCD screen, keyboard, and touchpad
- Comes with (x8) 6 ft. USB/PS2 combo KVM cable kits
- Features an additional USB 1.1 peripheral port
- OSD available in English, Spanish, French, German, and Japanese
- Compatible with all major operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- Computer with a HD15 port, and a USB port or PS/2 keyboard/mouse ports
- A P778-Series USB/PS2 combo KVM cable kit is required for each connected computer/server
- Compatible with all major operating systems

### Package Includes

- B020-U08-19KTAA 1U rackmount console with built-in 8-Port KVM switch, 19" LCD, keyboard, and touchpad
- (x8) P778-006 6 ft. USB/PS2 combo KVM cable kits
- USB/PS2 combo console cable kit
- RJ11 to DB9 firmware upgrade cable
- C13 to 5-15P power cord
- CD with owner's manual
- Quick start guide
- Grounding wire
- Rackmount hardware



- Two level password security (up to 1 Administrator and 4 User accounts)
- Supports video resolutions up to 1280 x 1024
- Firmware upgradeable
- Compatible with all major operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Constructed of heavy-duty steel housing

## Specifications

OVERVIEW	
# Of Users	1
Console	Yes
Port Control	Push Buttons, Hotkeys, OSD
Max CPU	8
PC/Server	PS/2
IP Remote Access	No
Style	1U Rackmount Console
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 17 x 27
Unit Dimensions (hwd / cm)	4.45 x 43.18 x 68.58
Unit Weight (lbs.)	30.6
Unit Weight (kg)	13.88
Included Mounting Accessories	Yes
Color	Black
LCD Monitor (in.)	19
LCD Monitor (cm)	48.26
ENVIRONMENTAL	
Storage Temperature Range	-4 Degrees F to 140 degrees F (-20 to +60 C)
Relative Humidity	0 to 80% RH, Non-condensing
Operating Temperature	32 Degrees F to 120 Degrees F (0 to 50 C)
CONNECTIONS	
Ports	8
Computer/Server Ports	(x8) HD18 (Female)
Firmware Upgrade Port	RJ45 Female



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Included Cable (Side A) - Connector 1	HD18 Male
Included Cable (Side B) - Connector 1	HD15 Male
Included Cable (Side B) - Connector 2	PS/2 Male
Included Cable (Side B) - Connector 3	PS/2 Male
Included Cable (Side B) - Connector 4	USB A Male
Other Ports - Port 1	USB A for Optional USB Keyboard/Mouse connection
Other Ports - Port 2	USB A for USB peripheral connection (e.g. Flash drive)
Remote Console Port	PS2/USB Combo Console Cable Kit w/VGA, (x2) PS2 & (x2) USB Female connectors
<b>FEATURES/SPECIFICATIONS</b>	
Autoscan (Y,N)	Y
<b>CERTIFICATIONS</b>	
Approvals	UL, cUL, CE, FCC, RoHS, TAA
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.