

2-Port HDMI Splitter for Video with Audio 1920x1200 at 60Hz / 1080p (HDMI F/2xF)

MODEL NUMBER: **B118-002**



Description

Tripp Lite's B118-002 HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device to be displayed on two HDMI displays, or, connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's [P566-Series](#) cables. Installation is quick and simple, with no software or drivers to install. Locate your HDMI source up to 13 ft. (4 m.) from the splitter, and the splitter up to 16 ft. (5 m.) from a display, for a max distance of 29 ft. (9 m.) between source and display. Multiple splitters can be cascaded together to connect additional monitors, with no more than 6 levels of splitters in all. Supports HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200. High Speed HDMI and 3D compliant, with support for 36-bit Deep Color (12-bits per channel). Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio. HDCP and EDID compliant.

Features

- Transmit a HDMI signal from a single source to two displays
- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- High Speed HDMI and 3D compliant
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- HDCP and EDID compliant
- Plug and play; No software or drivers required
- Locate a monitor up to 29 ft. (9 m.) from a HDMI source; up to 13 ft. (4 m.) between the source and the switch; up to 16 ft. (5 m.) between the switch and a monitor
- Cascade multiple levels of splitters together to increase the number of connected monitors, with no more than 6 levels of splitters in all
- Connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's [P566-Series](#) cables.

Specifications

Highlights

- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- High Speed HDMI and 3D compliant
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- HDCP and EDID compliant
- Plug and play; No software or drivers required

Applications

Retail, Classroom, Movie Theaters...anywhere a HD signal needs to be broadcast to multiple digital displays

System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 13 ft. (4 m.)
- The cable connecting the splitter to a HDMI monitor must be no longer than 16 ft. (5 m.)

Package Includes

- B118-002 2-Port HDMI Splitter
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 1.2A)
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
Display Style	Splitter
Model Type	HDMI
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	HDMI (FEMALE) (X2)
Number of Connectors	3
Ports	2
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.