

## DVI Extender Equalizer, Single-Link Video Repeater, 1920x1200 at 60Hz / 1080p (DVI F/F)

MODEL NUMBER: **B120-000-SL**



### Highlights

- Extend a DVI-D Single-Link signal up to 150 ft. from the source
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- Use P561-Series DVI Single-Link cables in most applications.
- When extending a 1920 x 1200 (or 1080p) video signal more than 75 ft., use cable made with 24Awg wiring
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B120-000-SL DVI Single Link Extender
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Screwdriver for equalization adjustment
- Owner's Manual

### Description

Tripp Lite's B120-000-SL DVI Single-Link Signal Extender increases the distance a DVI-D signal can be transmitted beyond the recommended 16 ft. (5 m.). Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p, as well as a maximum distance of 150 ft. from the source. Use P561-Series DVI Single-Link cables in most applications. When extending a 1920 x 1200 (or 1080p) video signal more than 75 ft., use cable made with 24Awg wiring. (Available from Tripp Lite as a custom order) Simply connect the longer cable between the source and the B120-000-SL, and the shorter cable (16 ft. or less) between the adapter and the monitor. Software or drivers are not required. Built-in Equalization control to adjust the video image. HDCP and DDC compatible. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Extend a DVI-D Single-Link signal up to 150 ft. from the source
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p.
- Use P561-Series DVI Single-Link cables in most applications
- When extending a 1920 x 1200 (or 1080p) video signal more than 75 ft., use a cable made with 24Awg wiring (Available from Tripp Lite as a custom order)
- Built-in Equalization control to adjust the video image
- HDCP and DDC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

General Info	
RoHS	Y



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>OVERVIEW</b>	
Chromebook Compatible	No
Display Style	Signal Booster
Model Type	DVI
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	DVI-I (FEMALE)
Connector B	DVI-I (FEMALE)
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.