

HDMI over Dual Cat5/Cat6 Extender Kit, In-Line Transmitter and Receiver for Video and Audio, 1920x1200 1080p at 60Hz (HDMI M/F)

MODEL NUMBER: **B125-101-60**



Description

Tripp Lite's HDMI Over Dual Cat5 Extender Kit is the perfect solution for those who need to extend a HDMI signal over a long distance over two Cat5/6 cables.

- When using 24Awg, Solid Wire Cat6 cable, a 1080p @ 60Hz (or 1920 x 1200) signal can be extended up to 150 ft. from the source.
- When using 24Awg, Solid Wire Cat6 cable, a 3D signal can be extended up to 125 ft.
- When using 24Awg, Solid Wire Cat5 cable, a 1080p @ 60Hz (or 1920 x 1200) signal can be extended up to 100 ft. from the source.
- When using 24Awg, Solid Wire Cat5 cable, a 3D signal can be extended up to 75 ft.

Simply run two Cat5/6 cables between the local transmitter and remote receiver units, and plug in standard Tripp Lite HDMI cables to the HDMI source and the display.

The B125-101-60 comes with both local transmitter and remote receiver units. DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio are supported, and it is compliant with HDCP, EDID and DDC. 24-bit True Color (8-bits per channel) is supported. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 150 ft. using 24Awg, Solid Wire Cat6 cabling (Tripp Lite N202-Series)
- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 100 ft. using 24Awg, Solid Wire Cat5 cabling
- Extends a 3D signal up to 125 ft. using 24Awg, Solid Wire Cat6 cabling, or up to 75 ft. using 24Awg, Solid Wire Cat5 cabling
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC
- Supports 24-bit True Color (8-bits per channel)

Highlights

- Extends a 1080p @ 60Hz (or 1920 x 1200) signal up to 150 ft. using 24Awg, Solid Wire Cat6* cabling (Tripp Lite N202-Series)
- Extends a 3D signal up to 125 ft. using 24Awg, Solid Wire Cat6* cabling (Tripp Lite N202-Series)
- Supports 24-bit True Color (8-bits per channel)
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

*When using Cat5 cable, the maximum extension distance is reduced by 50 ft.

Package Includes

- Local Transmitter and Receiver Units
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A - Output: 5V, 2A)
- Screwdriver for Equalization adjustment
- Owner's Manual



- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor
- Equalization control dial for skew compensation
- Supports Lip-Sync Pass Through, and CEC pass through
- Green LED indicate power being received
- Orange LED indicates signal connection
- Compliant with the Federal Trade Agreements Act (TAA) for GSA schedule purchases

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	Yes
Display Style	Extender
Model Type	HDMI
Cable Types	CAT5/CAT5E
PHYSICAL	
Unit Dimensions (hwd / in.)	Remote Unit: 2.375"W x 1.75"D x 0.75"H Source Unit: 2.375"W x 1.75"D x 0.75"H
Unit Dimensions (hwd / cm)	6.03 x 4.45 x 1.9
Color	Black
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	RJ45 (FEMALE) (X2)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.