


VGA over Cat5/Cat6 Extender Kit, Box-Style Transmitter and Repeater, 1920x1440 at 60Hz, Up to 1000-ft.

MODEL NUMBER: **B130-111**



Description

Tripp Lite's B130-111 extender/repeater kit comes with both local transmitter and remote/repeater units. By connecting additional receiver ([B132-100-1](#) or [B132-100-WP-1](#)) or repeater ([B132-110](#)) units, you can locate multiple monitors at different points in a chain of up to 2,000 ft.. With Tripp Lite's standard transmitters and receivers, a single VGA monitor can be located up to 1,000 ft. from the source. By inserting a remote/repeater unit in between, the signal can be regenerated and extended to another monitor up to an additional 1,000 ft. away. A monitor can be connected to both the remote/repeater and the receiver, allowing the signal to be transmitted to both points in the chain. Up to 4 remote units (3 remote/repeaters and 1 receiver) can be connected together, providing video to up to 4 remote displays located at different points in the installation. 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution. For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#).

Equalization and Gain controls are built into the remote/repeater unit for the adjustment of the video image. Mounting hardware is included for both the local and remote units, allowing them to be wall mounted, rackmounted, or pole mounted. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Kit comes with both local transmitter and remote/repeater units.
- Locate multiple monitors at different points in a chain of up to 2,000 ft. by connecting additional receiver ([B132-100-1](#) or [B132-100-WP-1](#)) or repeater ([B132-110](#)) units
- Up to 4 remote units (3 repeaters and 1 receiver) can be connected together, providing video to up to 4 remote displays
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is

Highlights

- Kit comes with both local transmitter and remote/repeater units
- Locate multiple monitors at different points in a chain of up to 2,000 ft. by connecting additional receiver ([B132-100-1](#) or [B132-100-WP-1](#)) or repeater ([B132-110](#)) units
- Up to 4 remote units (3 repeaters and 1 receiver) can be connected together, providing video to up to 4 remote displays
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Locate multiple monitors at different points in a chain of up to 2,000 ft. by connecting additional remote receiver ([B132-100-1](#) or [B132-100-WP-1](#)) or remote/repeater ([B132-110](#)) units to the remote/repeater included with the B130-111 kit.

System Requirements

- Computer with VGA video output
- Monitor / TV with VGA video input

Package Includes

- B130-111 local transmitter unit
- B130-111 remote/repeater unit



required to achieve maximum distance and resolution

- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Extend a 1920 x 1440 (60Hz) signal up to 500 ft., or a 1024 x 768 (60Hz) signal up to 1,000 ft., between the local transmitter and the first remote/repeater in the installation.
- Extend a 1920 x 1440 (60Hz) signal up to an additional 500 ft., or a 1024 x 768 (60Hz) signal up to an additional 1,000 ft., from the first remote/repeater unit to the last display in the installation.
- Features built-in Equalization and Gain controls for video image adjustment.
- Includes mounting hardware that allows wall mounting, rackmounting or pole mounting.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

- (x2) 5V, 2A external power supply
- Screwdriver for video adjustment
- Mounting hardware
- Owner's manual

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	No
Display Style	Extender
Model Type	VGA
Cable Types	CAT5/CAT5E
PHYSICAL	
Shipping Weight (lbs.)	2.0
Shipping Weight (kg)	0.91
Included Mounting Accessories	Yes
Color	Black
CONNECTIONS	
Connector A	HD15 (FEMALE) (X3)
Connector B	RJ45 (FEMALE) (X3)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.