

External 48V 3U Rack/Tower Battery Pack Enclosure + DC Cabling for select UPS Systems (BP48V60RT-3U)

MODEL NUMBER: **BP48V60RT-3U**



Description

BP48V60RT3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 48V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 48V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - SM2200RMDVTAA, SMART1500CRMXL, SMART2200CRMXL, SMART2200RMXL2U, SMART2200RMXL2UP, SMART2200RMXLN, SMART2200VSXL, SMART2600RM2U, SMART3000CRMXL, SMART3000RM2U, SMART3000RM2UN, SMART3000RMXL2U, SMART3000RMXLN, SMART3000VS, SMART5000RT3U, SMART5000XFMRXL, SMARTINT3000VS, SMX2200XLRT2U, SMX3000XLRT2U, SMX3000XLRT2UA, SMX5000XLRT3U, SU1500RTL2UA, SU1500RTLCD2U, SU1500XL, SU1500XLCD, SU2200RTL2UA, SU2200RTLCD2U, SU2200XLA, SU2200XLCD, SUINT1500RTL2UA, SUINT2200RTL2UA and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 48V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 48V external battery packs to the host UPS
- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced 2 point center-mounting in 2 post equipment racks
- 2-9USTAND option enables upright tower placement

Specifications

General Info

Highlights

- Extends the runtime of expandable 48V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

Applications

- Ideal means of lengthening the battery runtime provided by compatible Tripp Lite UPS systems

Package Includes

- BP48V60RT-3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

RoHS	Y
BATTERY	
Expandable Battery Runtime	Blue 175 amp female connector for additional battery packs
DC System Voltage (VDC)	48
UPS Connection	20 inch attached cable with blue 175 amp male DC connector
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITHD); Tower (2-9USTAND)
Shipping Dimensions (hwd / in.)	11.5 x 23 x 33
Shipping Dimensions (hwd / cm)	29.2 x 58.4 x 83.8
Shipping Weight (lbs.)	200.6
Shipping Weight (kg)	91.1
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 25
Unit Dimensions (hwd / cm)	13.3 x 44.4 x 63.5
Unit Weight (lbs.)	163.1
Unit Weight (kg)	74
Material of Construction	Steel
ENVIRONMENTAL	
Operating Temperature	32-104 degrees F / 0-40 degrees C
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.