

VGA with Audio over Cat5/Cat6 Extender, Box-Style Receiver, 1920x1440 at 60Hz, Up to 1000-ft.

MODEL NUMBER: **B132-100A**



Description

Tripp Lite's B132-100A works with a [B132-002A](#) or [B132-004A](#) local transmitter unit to extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft.. 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution. For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#). Features built-in Equalization and Gain controls to adjust the video image. Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted. Ideal for digital signage situations, such as retail, schools, churches, etc. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Works with a [B132-002A](#) or [B132-004A](#) local unit to extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft.
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Features built-in Equalization and Gain controls to adjust the video image
- Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted
- Ideal for digital signage situations, such as retail, schools, churches, etc..
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 1 year limited warranty.

Highlights

- Works with a [B132-002A](#) or [B132-004A](#) local unit to extend a 1920 x 1440 (60Hz) Video and Audio signal up to 500 ft., or a 1024 x 768 (60Hz) Video and Audio signal up to 1,000 ft.
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Extender remote (Receiver) unit
- Mini-Screwdriver for EQ/Gain adjustment
- Mounting Hardware
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's Manual

Specifications

General Info



RoHS	Y
OVERVIEW	
Chromebook Compatible	No
Display Style	Splitter
Model Type	VGA
Cable Types	CAT5/CAT5E
PHYSICAL	
Shipping Weight (lbs.)	1
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	1 x 2.5 x 3.6
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.14
Unit Weight (lbs.)	0.45
Unit Weight (kg)	0.20
Color	Black
CONNECTIONS	
Connector A	HD15 (FEMALE)
Connector B	3.5MM (FEMALE)
Connector C	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.