

DVI over Cat5/Cat6 Active Extender, Box-Style Remote Video Receiver, 1920x1080 at 60Hz

MODEL NUMBER: **B140-1A0**



Description

The B140-1A0 is a receiver unit that is used with the [B140-002](#) and [B140-004](#) extender/splitter transmitter units, and it transmits a DVI-D Single-Link signal up to 200 ft. away using a single Cat5e/6 patch cable. To achieve maximum distance and resolution, use 24AWG Solid Wire Cat5e/6 cable (Tripp Lite's [N202-Series](#)). The B140-1A0 is compatible with all operating systems, and is plug and play, with no software or drivers required. It features a built-in Equalization control for adjustment of the video image. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation is simple. Connect a [B140-002](#) or [B140-004](#) transmitter (not included) to a DVI source using a Tripp Lite [P561-Series DVI cable](#) (not included). Connect the B140-1A0 to a display using a Tripp Lite [P561-Series DVI cable](#) (not included). Finally, the receiver unit is connected to an RJ45 port on the transmitter unit using a single Cat5e/6 cable. A 1920 x 1080 @ 60Hz signal can be extended up to 150 ft. from the source, or a 1024 x 768 @ 60Hz signal up to 200 ft.

Further expand the range and number of monitors by using a [B140-110](#) repeater unit. Add up to four remote units (three repeaters and one active receiver) to each channel of the B140-002 or B140-004, for a total of 4 displays per channel. (An active receiver should be the last unit in a channel) A 1920 x 1080 @ 60Hz signal can be extended up to 125 ft. from each repeater to the next unit in the channel, or a 1024 x 768 @ 60Hz signal can be extended up to 175 ft.

Features

- Transmit a DVI-D Single-Link signal up to 200 ft. away using a single Cat5e/6 patch cable
- For use with [B140-002](#) or [B140-004](#) extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 150 ft., or a 1024 x 768 @ 60Hz signal up to 200 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N202-Series](#), to achieve maximum distance and resolution

Highlights

- For use with [B140-002](#) or [B140-004](#) extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 150 ft., or a 1024 x 768 @ 60Hz signal up to 200 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N202-Series](#), to achieve maximum distance and resolution
- Can further expand the range and number of monitors by adding [B140-110](#) repeaters
- Compatible with all operating systems
- Plug and play, no software or drivers required
- Features a built-in Equalization control for adjustment of the video image
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B140-1A0 DVI over Cat5 Active Extender Remote Unit
- Mounting hardware
- Screwdriver for adjustment of Equalization
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's Manual



- Features a built-in Equalization control for adjustment of the video image
- Further expand the range and number of monitors by using a [B140-110](#) repeater unit
- Add up to four remote units (three repeaters and one active receiver) to each channel of the B140-002 or B140-004, for a total of 4 displays per channel. (An active receiver should be the last unit in a channel)
- A 1920 x 1080 @ 60Hz signal can be extended up to 125 ft. from each repeater to the next unit in the channel, or a 1024 x 768 @ 60Hz signal can be extended up to 175 ft.
- HDCP compatible
- Compatible with all operating systems
- Plug and play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	No
Display Style	Splitter
Model Type	DVI
Cable Types	CAT5/CAT5E
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 2.5 x 3.6
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.14
Included Mounting Accessories	Yes
CONNECTIONS	
Connector A	RJ45 (FEMALE)
Connector B	DVI-I (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.