

## Easy Pull Long-Run Display Cable - Type-A Analog Plenum Trunk Cable, 50-ft.

MODEL NUMBER: **EZA-050-P**



### Description

Tripp Lite's EZA-050-P 50 ft. Easy Pull VGA Plenum Trunk Cable makes pulling video cable through conduit or confined areas a breeze. Plenum-rated jacket complies with local fire codes. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from a variety of connector choices that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 35 ft., 50 ft. and 100 ft. lengths, both PVC and plenum rated. Cable ends are colored-coded green to denote VGA applications (Digital trunk cables are Yellow). Cable features triple-shielded construction with 75 ohm coax conductors for RGBHV signals supporting resolutions up to 1600 x 1200. Trunk also carries Audio signals when used with Easy Pull end kits that feature Audio connections.

### Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connectors
- Plenum-rated jacket complies to local fire codes
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35 ft., 50 ft. and 100 ft., both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

## Specifications

General Info	
RoHS	Y
OVERVIEW	

### Highlights

- Versatile trunk cable allows for a variety of connection options
- Plenum-rated jacket to comply with local fire codes
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

### Applications

- Use where standard VGA cables won't fit, such as conduit or confined wall or ceiling spaces

### Package Includes

- Easy Pull Type-A VGA Analog Plenum Trunk Cable, 50 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Chromebook Compatible	No
Display Style	Easy Pull
Model Type	VGA
Cable Types	CAT6
<b>INPUT</b>	
Cable Length (ft.)	50
Cable Length (m)	15.24
<b>PHYSICAL</b>	
Color	Black; Green
<b>CONNECTIONS</b>	
Connector A	EASY PULL A (FEMALE)
Connector B	EASY PULL A (FEMALE)
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.