

Easy Pull Type-A Connectors - F/F set of VGA,3.5mm,RCA Audio,Composite Video

MODEL NUMBER: **EZA-VGACSAF-2**



Description

Easy Pull Connector Kit includes: 2 x HD15 Female, 2 x stereo 3.5mm jack, 4 x RCA Red/White Audio jacks, and 2 x Yellow Composite Video jack, with 2 x faceplates and 1 ft. pigtails. Video support up to 1600 x 1200. Use with either PVC or Plenum Easy Pull trunk cables.

Features

- Easy Pull, SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Female to Female
- Eliminates the need to field terminate VGA connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. lengths, PVC or Plenum rated jackets
- Support resolutions up to 1600 x 1200

Specifications

OVERVIEW	
Display Style	Easy Pull
Model Type	VGA
Cable Type	CAT6
UPC ASSIGNMENT	
Unit Carton UPC#	037332153784

Highlights

- SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Female to Female
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

Applications

- Use where standard VGA cables won't fit, such as conduit or confined wall or ceiling spaces

Package Includes

2 x HD15/3.5mm/Red White RCA Audio/Composite Video, All female Jacks, with wallplates



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	HD15 Female
Side A - Connector 2	3.5mm Female
Side A - Connector 3	2 x RCA Female - Red White Audio
Side A - Connector 4	RCA Female - Composite Video
Side B - Connector 1	Din 14 Pin Male
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.