

Easy Pull Type-A Connectors (F/F set of VGA with Faceplates)

MODEL NUMBER: **EZA-VGAF-2**



Description

Easy Pull Connector Kit includes: 2 x HD15 Female - 1 ft. pigtails and 2 Wall plates. Easy Pull trunk run with a finished appearance. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

Features

- Eliminates the need to field terminate VGA connectors
- Wall plates with HD15 cut-out cleanly finishes off the cable run
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35ft, 50ft and 100ft PVC lengths, and 35ft and 50ft Plenum jackets
- Supports resolutions up to 1600 x 1200

Specifications

OVERVIEW	
Intended Application	Connecting Devices
Display Style	Easy Pull
Model Type	VGA
Cable Type	CAT6
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30

Highlights

- SVGA Connector Kit, Female to Female -HD15, 2 x Wall plates
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200
- Easily pulls through conduit or confined spaces with included pull-caps

Applications

- Use where standard VGA cables won't fit, such as conduit, or confined wall or ceiling spaces

Package Includes

- Type-A Easy Pull Kit w/HD15 F/F, 1 ft. pigtails & (2) Wall plates



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC ASSIGNMENT	
Unit Carton UPC#	037332142832
CONNECTIONS	
Connector A	HD15 (FEMALE)
Connector B	HD15 (FEMALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.