

Easy Pull Type-A Connectors - (M/F set of VGA with Faceplate)

MODEL NUMBER: **EZA-VGAX-2**



Description

Easy Pull Connector Kit includes: HD15 Male & HD15 Female - 1 ft. pigtail and Wall Plate. Completes your Easy Pull trunk run with a finished appearance. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

Features

- Eliminates the need to field terminate VGA connectors
- Wall plate with HD15 cut-out cleanly finish off the cable run
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35. ft, 50. ft, and 100 ft. PVC lengths, and 35 ft. and 50 ft. Plenum jackets
- Supports resolutions up to 1600 x 1200

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	No
Display Style	Easy Pull
Model Type	VGA
Cable Types	CAT6

Highlights

- SVGA Connector Kit, Male to Female - HD15, Wall Plate
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

Applications

- Use where standard VGA cables won't fit, such as conduit or confined wall or ceiling spaces

Package Includes

- HD15 Male 1 ft. pigtail
- HD15 Female 1 ft. pigtail
- Wall plate w/HD15 cut-outs



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (FEMALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.