

48-Port 2U Rack-Mount Cat5e 110 Patch Panel, 568B, RJ45 Ethernet

MODEL NUMBER: **N052-048**



Highlights

- 19-in. rackmount ready, 2U Height (3.50in)
- EIA/TIA 2/32 spacing
- 110 type punchdown termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat5e Patch Panel 568B-48 Port, 2U

Description

Tripp Lite's Enhanced Category 5 Patch Panels offer you all the functionality and compatibility as any name brand. Each panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Cat5e connecting hardware specifications. Color coded for both EIA/TIA 568A & 568B installations. 48 ports ensure a wide range of plug-n-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs and the high density 19in panel design will save you valuable space in on the rack.

Features

- Cat5e
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Rack mountable on a 19 rack (2U Height, 3.50in)

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Cat5/5e
Model Type	Patch Panels



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Connector A	110-TYPE TERMINAL (X48)
Connector B	RJ45 (FEMALE) (X48)
KVM Connector 1	(x12) RJ45 (Female)
KVM Connector 2	(x12) RJ45 (Female)
Ports	48
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.