

5 outlet, direct plug-in, 1080 joules, 1-line RJ 11 protection - Protect It! Surge Suppressor

MODEL NUMBER: **SK5TEL-0**



Highlights

- 5 outlets / direct plug-in
- 1080 joule rating
- Tel/DSL Surge Protection
- Diagnostic LEDs
- \$15,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC power protection

Package Includes

- SK5TEL-0 surge suppressor
- 6-ft phone cord

Description

The SK5TEL-0 surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 5 outlets and 1080 joules of surge energy absorption. Set of RJ11 telephone line suppression jacks protect dial-up and DSL modem lines, fax machines, cordless phones and more. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$15,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 5 outlets / direct plug-in
- Surge suppression rating: 1080 joules
- 1 in/1 out Tel/DSL surge protection
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$15,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Intended Application	Home / Office
Style	Direct plug-in
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Circuit Breaker (amps)	15



Outlet Quantity / Type	5 NEMA5-15R
Number of Outlets	5
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120v
Input Connection Type	NEMA 5-15P
Input Plug Features	120V, 15A
Input Cord Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
UPC ASSIGNMENT	
Unit Carton UPC#	037332167477
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500, 500, 400
EMI / RFI Filtering	up to 45dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
PHYSICAL	
Unit Dimensions (hwd / in.)	5 x 3.5 x 2.1
Unit Dimensions (hwd / cm)	12.7 x 8.89 x 5.33
Unit Weight (lbs.)	.33
Unit Weight (kg)	.15
Material of Construction	Plastic
Housing Color	Light Gray
Receptacle Color	Light Gray
CERTIFICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
cUL / CSA (Canada)	cUL
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$15,000 Ultimate Lifetime Insurance

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.