

## Waber-by-Tripp Lite 6-Outlet (75.9mm center-to-center spacing) Industrial Power Strip, 6-ft. Cord

MODEL NUMBER: **6NX6**



### Description

Tripp Lite's 6NX6 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing, 6-ft. AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 6NX6 ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige housing with black receptacles.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation on a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-ft. AC line cord

## Specifications

### General Info

### Highlights

- 6 outlets
- 6-ft. cord
- 12.5-in. length
- Master on/off switch
- All-metal housing

### Applications

- Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes the 6NX6 ideal for distributing alternate waveform UPS or generator power to protected equipment.

### Package Includes

- 6NX6 Power Strip
- Warranty information
- Instruction manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

RoHS	Y
<b>OVERVIEW</b>	
Style	Strip
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Outlet Spacing	1.520 in.
Outlet Orientation	Single row of 6
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8288
Voltage Compatibility (VAC)	120
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted combination switch / circuit breaker
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Black
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	75.9mm
Keyhole Slot Mounting Measurement (Center to Center)	240mm
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.