

Internet Office 120V 550VA 300W Standby UPS, Ultra-Compact Desktop, USB port

MODEL NUMBER: **INTERNET550U**



Description

Tripp Lite's INTERNET550U standby UPS offers complete protection for PCs, workstations and other sensitive electronics in an attractive ultra-compact, mountable housing. Prevents data loss and system downtime by providing battery supported AC output during brownouts and blackout conditions. 8 output receptacles, two of which are widely-spaced to accommodate large transformer plugs without blocking outlets. 4 outlets with full battery support and surge suppression protect computers, monitors and other vital system components from loss of power. 4 additional outlets with surge suppression-only are ideal for printers and other accessories not requiring battery support. Single line telephone suppression jacks protect modem, fax machine, cordless phone or other peripherals with a standard dialup or DSL phone line connection. USB port with PowerAlert monitoring software (available via web download) and cabling enables safe unattended system shutdown in the case of extended power failure. HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X. Audible alarm and front panel LEDs offer status information regarding line and battery power operation. 550VA/300 watt power handling ability supports an entry level PC with small monitor consuming 100 watts for up to 10 minutes during power failures. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- INTERNET550U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and Tel/DSL line connections
- 8 outlets, two of which are widely spaced to accommodate large transformer plugs without blocking outlets
- 4 battery supported outlets protect computer, monitor and vital system peripherals, plus 4 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 550VA/300 watt power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports an entry level PC with small monitor consuming 100 watts for up to 10 minutes during power failures
- Built-in single line Tel/DSL line surge suppression protects modem, fax machine or cordless phone
- USB port, PowerAlert software (available via web download) and cabling offer safe unattended shutdown without data loss during extended outages
- HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X.
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications

Highlights

- 550VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 4 UPS battery supported outlets, 4 surge-only outlets
- USB port, TEL/DSL protection, Wall mountable, 99% efficient
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets
- **This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment**

Package Includes

- INTERNET550U UPS System
- USB cable
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Space saving, ultra-compact housing fits almost anywhere
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Keyhole mounting flanges enable secure wallmount installation

Specifications

General Info	
RoHS	Y
OUTPUT	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (Watts)	300
Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacles	(8) 5-15R
UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 4 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	10A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Half Load Runtime (min.)	5.6 minutes (150w)
DC System Voltage (VDC)	12



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination switch controls on/off power status and self-test operation
Audible Alarm	Audible alarm indicates power-failure and overload status
LED Indicators	2 LEDs indicate power status and overload/check battery status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	420
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	3.1 x 5.7 x 10.8
UPS Power Module Dimensions (hwd, cm)	7.8 x 14.6 x 27.6
UPS Power Module Weight (lbs.)	5
UPS Power Module Weight (kg)	2.3
UPS Shipping Dimensions (hwd / in.)	4.1 x 8 x 13
UPS Shipping Dimensions (hwd / cm)	10.4 x 20.3 x 33
Shipping Weight (lbs.)	5.5
Shipping Weight (kg)	2.5
UPS Housing Material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	14
Battery Mode BTU / Hr. (Full Load)	194.3
AC Mode Efficiency Rating (100% Load)	99%



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

COMMUNICATIONS	
Communications Interface	USB (HID enabled)
PowerAlert Software	Free download from www.tripplite.com
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
LINE / BATTERY TRANSFER	
Transfer Time	4 milliseconds (AC to battery mode) / 2 milliseconds (battery mode to AC)
Low Voltage Transfer to Battery Power (Setpoint)	99
High Voltage Transfer to Battery Power (Setpoint)	139
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); ENERGY STAR Qualified
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.