

VERSO**SIDE OPENING POLYCARBONATE HOUSING****MAIN FEATURES**

IP66/IP67 (with cable glands or optional sealing rings)

Vandalproof protection (IK10)

Pre-arranged for internal cable management bracket

Version with a very efficient cooling system for installation with IP cameras and for high environmental temperature

Available accessories: heater, camera power supply, fan assisted heater, washer pump

DESCRIPTION

Sturdy tamper-proof housing designed to simplify the installation and service and guarantee total protection against all environmental conditions.

Its dimensions make it suitable for a variety of combinations of cameras and lenses.

Entirely constructed from technopolymer, it guarantees high impact resistance, high weather protection from external agents and UV rays.

Very easy to install thanks to the side opening system that allows the full access to the camera, lenses and all internal connections.

A specific version with a very efficient cooling system is available for installations with IP cameras and for high environmental temperature.

A wide range of accessories for mounting the equipment is available thereby satisfying all installation needs.

The housing proposes various mounting options, wall or ceiling brackets, feedthrough and non-feedthrough, or Pan & Tilt head.



VERSO COMPACT



VERSO + CAMERA



VERSION WITH COOLING DEVICE

AVAILABLE MODELS

Model Number	Sunshield	Heater 120Vac/230Vac	Heater 12Vdc/24Vac	12Vdc fan with double air exchange filter	24Vac fan with double air exchange filter	Max consumption
HPV42K0A000	✓	—	—	—	—	—
HPV42K1A000	✓	✓	—	—	—	40W
HPV42K2A000	✓	—	✓	—	—	20W
HPV42K2A016	✓	—	✓	—	✓	24W
HPV42K2A017	✓	—	✓	✓	—	24W

TECHNICAL DATA
GENERAL
Entirely made of technopolymer (polycarbonate)
Sunshield in ABS
RAL9002 Colour
Stainless steel external screws
MECHANICAL
Cable glands: 3xM16
Polycarbonate window (WxH): 105x64mm (4.1x2.5in)
Internal usable area (WxH): 70x70mm (2.7x2.7in)
Internal usable length (with or without accessories): 270mm (10.6in)
Unit weight: 1.5kg (3.3lb)
ELECTRICAL
Power supply/Current consumption (empty version):
- From 12Vdc to 24Vdc, 1A max - From 12Vac to 24Vac, 1A max, 50/60Hz - From 120Vac to 230Vac, 400mA max, 50/60Hz
Power supply/Current consumption (version with heater, Ton 15°C±3°C (59°F±5°F), Toff 22°C±3°C (77°F±5°F)):
- From 12Vdc to 24Vdc, 5A max - From 12Vac to 24Vac, 5A max, 50/60Hz - From 120Vac to 230Vac, 700mA max, 50/60Hz
Power supply/Current consumption (version with heater fan assistant, continuous duty):
12Vdc, 400mA max 24Vac, 200mA max, 50/60Hz - From 100Vac to 240Vac, 40mA max, 50/60Hz (with wide-range power supply)
Power supply/Current consumption (version with blower and thermostat for models with double filter for air renewal, Ton 35°C±3°C (95°F±5°F), Toff 20°C±3°C (71°F±5°F)):
12Vdc, 400mA max 24Vac, 200mA max, 50/60Hz
Camera power supply:
- V_{IN} from 100Vac to 240Vac, 50/60Hz - V_{OUT} 12Vdc, 1A - V_{IN} 230Vac, 50/60Hz - V_{OUT} 24Vac, 400mA, 50/60Hz
ENVIRONMENT
Indoor/Outdoor
Operating temperature (with heater): From -20°C (-4°F) to +60°C (140°F)
Chemical agents resistance
- High resistance: basics, alcohols, gas, hydrocarbon - Good resistance: Organic acids, inorganic acids, oils - Low resistance: Solvents
CERTIFICATIONS
CE: EN61000-6-3, EN50130-4, EN60950-1, EN60950-22
EN60529 IP66/IP67 (with cable glands)
EN60529 IP66/IP67 (with special gaskets and bracket with internal cable channel)
EN60529 IP55 (with bracket with internal cable channel)
EN60529 IP44 (for models with cooling blower and double filter)
Fire-self extinguish: UL94 V1
Impact resistance: EN62262 IK10
cULus Listed, TYPE 4X (except for versions with double filter for the air exchange)

ACCESSORIES

OHPVPOEIPM	Maintenance/retrofit kit for VERSO and VERSO Hi-PoE IPM housings
OHEH26	Heater 120Vac/230Vac for HOV, HTV, VERSO, VERSO COMPACT housings
OHEH27	Heating 12Vdc/24Vac for HOV, HTV, HTC, VERSO and VERSO COMPACT housings
OHPVV1	Heater fan assistant, continuous duty, IN 12Vdc, for VERSO and VERSO COMPACT housings
OHPVV2	Heater fan assistant, continuous duty, IN 24Vac, for VERSO and VERSO COMPACT housings
OHPVV3	Heater fan assistant, continuous duty, IN 100-240Vac, for VERSO and VERSO COMPACT housings
OHPVCF3	Blower with thermostat and air filter
OHEPS19B	Wide range camera power supply IN 100-240Vac - OUT 12Vdc, 15W, for VERSO, VERSO POLAR, VERSO COMPACT, HEG, HTG housings
OHEPS20	Camera power supply IN 230Vac - OUT 24Vac, 10VA, for VERSO, VERSO POLAR, VERSO COMPACT, HEG, HTG housings
OHEGBPS1B	Wide range camera power supply IN 100-240Vac - OUT 12Vdc in weatherproof box, 15W, for VERSO, VERSO POLAR, HEG, HTG housings
OHEGBPS2B	Camera power supply IN 230Vac - OUT 24Vac in weatherproof box, 10VA, for VERSO, VERSO POLAR, HEG, HTG housings
OHPVTA1	Tamper switch on board with tamper proof screws and key for VERSO housing
OWBIP2	Sealing rings kit (3xM16) IP66/IP67 for WBOVA2 and WCM4A2 brackets for PUNTO, HOV, HTV, HTC, VERSO, VERSO POLAR, VERSO COMPACT, HEB, HEK housings
OHEGBB	Weatherproof junction box
OSUPPIR	Bracket for mounting 1 GEKO IRH illuminator under the housing

RELATED PRODUCTS

PTH300	Horizontal/vertical Pan & Tilt
PTH900	Horizontal/vertical Pan & Tilt

BRACKETS AND ADAPTORS


WBJA	Ceiling bracket with ball joint
WBOVA2	Wall bracket with internal cable channel
WBOV3A2	Wall bracket with internal cable channel, counterplate and support box, not compatible with OHEBVF1, OHEBVF2 and OHEBVF3
WCM3A	Ceiling bracket with ball joint
WCM5A	Ceiling bracket with ball joint
WCM4A2	Ceiling bracket with internal cable channel
WFWCA	Column bracket with joint

SPARE PARTS

OHPVS42A000	Sunshield
DOTHPV01	Cable glands, screws and spacers for camera and lens
OHPV42CS04	Complete upper body

PACKAGE

Model Number	Weight	Dimensions (WxHxL)	Master carton
HPV42K1A000	1.8kg (4lb)	16.5X15.5X49cm (6.5x6.1x19.3in)	10

TECHNICAL DRAWINGS*Sizes in millimeters.*

VERSO

