



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




CLEANING PAD (QTY. 1)




UNIVERSAL GROUNDING STICKER (QTY. 2)




5cc TUBE ANTI-OXIDANT PASTE (QTY. 1)




#10-32 & M5  
BONDING STUD (QTY. 8 OF EACH)



#10-32 & M5  
BONDING NUT (QTY. 16 OF EACH)



FACTORY CRIMPED #6 AWG FRONT TO BACK RAIL JUMPER GREEN/YELLOW INSULATION (QTY. 2)



UNIVERSAL GROUND BAR - RGRB19U (QTY. 1) INCLUDES:  
- #12-24 HEX HEAD SCREWS (QTY. 20) PRE-ASSEMBLED

NOTES:

- 1. RETRO-FIT CABINET GROUNDING KIT  
PART NUMBERS: CGR630UA
- 2. PACKAGING: 1 KIT PER BOX
- 3. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
- 4. ALL COMPONENTS THAT MAKE UP THIS KIT  
ARE RoHS COMPLIANT.



LISTED  
GROUNDING AND BONDING EQUIPMENT



CERTIFIED

C41631\_00

								<div>PANDUIT CORP. TINLEY PARK, ILLINOIS</div>		
								RETRO-FIT CABINET GROUNDING KITS (CGR630UA) CUSTOMER DRAWING		
								UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ±      (.XXX) ± (.XX) ±     ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
								DRAWN BY JHNU	MAT'L:	SCALE NONE
00	1/06	JHNU	JMAR	DRAWING RELEASED	PC00276			DATE 1/06		DRAWING NO / CAD FILE
REV	DATE	BY	CHK	DESCRIPTION	ECN	PM	CUST	CHK'D		C41631
										DWG B SIZE