


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	WIRE/CABLE SIZE	MATERIAL	"B" +/- .050	"C" +/- .050	COLOR	MARKER S/ROLL
H100X025H1C	22-16 AWG WIRES	GMUHS31	1.00 [25.40]	0.25 [6.35]	WHITE	100
H100X025H2C	22-16 AWG WIRES	GMUHS31	1.00 [25.40]	0.25 [6.35]	YELLOW	100
H100X034H1C	18-12 AWG WIRES	GMUHS31	1.00 [25.40]	0.34 [8.64]	WHITE	100
H100X034H2C	18-12 AWG WIRES	GMUHS31	1.00 [25.40]	0.34 [8.64]	YELLOW	100
H100X044H1C	16-10 AWG WIRES	GMUHS31	1.00 [25.40]	0.44 [11.18]	WHITE	100
H100X044H2C	16-10 AWG WIRES	GMUHS31	1.00 [25.40]	0.44 [11.18]	YELLOW	100
H100X064H1C	12-6 AWG WIRES	GMUHS31	1.00 [25.40]	0.64 [21.34]	WHITE	75
H100X064H2C	12-6 AWG WIRES	GMUHS31	1.00 [25.40]	0.64 [21.34]	WHITE	75
H100X084H1C	8-1 AWG WIRES	GMUHS31	1.00 [25.40]	0.84 [21.34]	WHITE	75
H100X084H2C	8-1 AWG WIRES	GMUHS31	1.00 [25.40]	0.84 [21.34]	YELLOW	75

NOTES:

1. DIMENSIONS IN []
ARE IN MILLIMETERS.



										CAD FILENAME/LAYERS I00619HM_C10697_H100_P1_01.prt	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										CUSTOMER DRAWING P1 LABEL CASSETTE DIE CUT HEAT SHRINK LABEL	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XX) ± .030 (.XXX) ± .025 ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	2/9/11	RVU	ADD PN: H100X064H1C AND H2C.	6300	R					DRAWN BY RVU	MAT'L: SEE TABLE
0	4/21/08	RVU	DRAWING RELEASE	5403	R					DATE 4/22/08	DRAWING NO. C10697
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D M/L	DWG A SIZE