


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	"X"	"Y"	WEIGHT
TMB105-X	1.37 (34.8)	3.89 (98.9)	.54 LB/10 PCS (246 g/10 PCS)
TMB130-X		4.88 (123.9)	.66 LB/10 PCS (300 g/10 PCS)
TMB170-X		6.46 (164.1)	.90 LB/10 PCS (410 g/10 PCS)

- NOTES:
- * 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - 2. THIS PART ACCOMMODATES PAN-WAY TYPE TD RACEWAY.
 - 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

										CAD FILENAME/LAYERS		D34518_TMB_MTGBKT_C_01	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										TD RACEWAY MOUNTING BRACKET (TMB105, TMB130, TMB170) CUSTOMER DRAWING			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	07-11-94	DW	CEF	A. ADDED DIMENSIONS TO SLOT.	34518-24	CEF	CEF			DRAWN BY DW	MAT'L: 21 GA. (.032") COLD ROLLED STEEL	SCALE NONE	
R	12-01-93	DW	CEF	RELEASED TO PRODUCTION	34518-24	CEF				DATE 12-01-93		DRAWING NO. 34518-24	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP			CHK'D CEF	