

115-00030

Article Number: 115-00030

Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Black, 5/pkg



Download spec sheet

Base Data

Local Order Number	115-00030
Type	SpeedyTie (RTT750HR)
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• The heavy duty Speedy tie features a specially designed head and patented trigger to allow for repeated use in temporary bundling applications.• Additional design feature on the head allows excess strap to be tucked away after installation.
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.
Short Description	Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Black, 5/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	200.0 lbs
Minimum Tensile Strength (Metric)	888.0 N
Length L (Imperial)	29.6 "
Length L (Metric)	752.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.51 "
Width W (Metric)	13.0 mm
Bundle Diameter Min. (Imperial)	1.6 "
Bundle Diameter Min. (Metric)	40.0 mm
Bundle Diameter Max. (Imperial)	8.3 "
Bundle Diameter Max. (Metric)	210 mm
Thickness T (Imperial)	0.075 "
Thickness T (Metric)	1.9 mm

Logistics and Packaging

Quantity Per	pieces
Package Quantity (Metric)	5 Pieces
Carton Quantity	60 Pieces

Weight (Metric) 23.2 kg

Material and Specifications

Material Polyamide 6.6, high impact modified, scan black (PA66HIR(S))

Material Shortcut PA66HIR(S)

Flammability UL94 HB

Operating Temperature -40°F to +176°F (-40°C to +80°C)

ROHS Compliant Yes