

T30R1M4



Article Number: 111-03038

Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66, Brown, 1000/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	T30R1M4
Type	T30R
Color	Brown (BN)
Features and Benefits	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66, Brown, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135.0 N
Length L (Imperial)	5.8 "
Length L (Metric)	148.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14 "
Width W (Metric)	3.6 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.38 "
Bundle Diameter Max. (Metric)	35.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	5000
Weight (Metric)	0.7 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
US MILSPEC	MS3367-5-1
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	SAE - AS33671 UL-ZODZ E64139 Cage Code 53421
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes