

RT50S0M4



Article Number: 115-00035

Releasable Cable Tie, 6.5" Long, 50 lb Tensile Strength, PA66, Black, 1000/pkg

 RoHS

 Download spec sheet

Base Data

Local Order Number	RT50S0M4
Type	RT50S
Color	Black (BK)
Features and Benefits	The extended pawl allows for simple and quick release of the ties.
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force . For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Releasable Cable Tie, 6.5" Long, 50 lb Tensile Strength, PA66, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225.0 N
Length L (Imperial)	6.5 "
Length L (Metric)	165.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.6 mm
Height H (Imperial)	0.06 "
Height H (Metric)	1.4 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.38 "
Bundle Diameter Max. (Metric)	35.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes